


Mailing Address: PO Box 1674 Warsaw, IN 46581-1674 Phone: 844-SEYMOUR FAX: 574-267-8508 www.seymourmidwest.com Shipping Address: 2666 S Country Club Rd Warsaw, IN 46580

# **Smoother**Assembly Instructions





#### **Tools Needed for Assembly:**

7/16" wrench (two)


#### Parts Shipped with Unit:

- Head/Blade Assembly
- Threaded handle adapter or aluminum handle (not pictured)
- Gusset brace (set of 2) one gusset is labeled if unit comes with threaded handle adapter
- Bolt bag for braces





- 2. Position labeled gusset on bottom of adapter, as shown, and the other gusset on top of the adapter. If unit comes with handle, gussets are interchangeable.
- 3. Insert the two longest bolts through the top gusset, the handle/adapter and the bottom gusset. Insert the two shorter bolts through the two remaining holes on the frame.
- 4. Tighten all nuts, being careful not to over-tighten. Over-tightening hardware may result in crushing the handle, thereby compromising its strength.



- 1. Remove nuts on head, lift head off bolts, and remove used blade.
- 2. Replace o-rings on bolts if necessary.
- 3. Fit new blade onto bolts.
- 4. Fit head onto bolts.
- 5. Tighten nuts until head assembly is secure, being careful not to over-tighten.



All Seymour Midwest products carry a full warranty against manufacturer defects in quality and workmanship.

Products which have been abused or worn out from normal use are excluded from this warranty.

We reserve the right to replace or issue credit on an individual basis.

### REPLACEMENT PARTS LIST

See Reverse Side

## **SMOOTHER REPLACEMENT PARTS**

SP50026	Stainless steel blade – 3-1/4"x1/2"
SP10055	Head – 24"
SP30045	Strip – 24" – aluminum for securing blade
SA20172	Handle – 66" aluminum powder-coated w/ vinyl grip
SP20025	Threaded handle adapter
SA30009	Braces – gusset (set of 2)
SA60023	Bolt bag: 4 bolts, 4 loc nuts (for handle attachment)
RM60053	Bolt – 3/4" hex head (requires 5)
RM60001	Keps nut (requires 5)
RM60092	O-ring - #202 rubber (requires 5)